

Insulated Mounting Panel, AMI



This is an easy to machine mounting plate that will prevent undesired contact between electrical components and the enclosure.

FEATURES

Description: Insulated mounting plate for wall mounted enclosures. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Bakelite.

Pack quantity: 1 piece.

Material: Bakelite
Finish: Smooth
Color: Black
Thickness: 4mm

SPECIFICATIONS

Table 1/2

Catalog Number	E-Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI02020	2502242	200mm	200mm	4mm	170 x 150mm	Mild Steel
AMI02520	2502243	250mm	200mm	4mm	220 x 150mm	Mild Steel
AMI02525	2502244	250mm	250mm	4mm	220 x 200mm	Mild Steel
AMI03025	2502245	300mm	250mm	4mm	270 x 200mm	Mild Steel
AMI03030	2502246	300mm	300mm	4mm	270 x 250mm	Mild Steel
AMI03040		300mm	400mm	4mm	270 x 350mm	Mild Steel
AMI03525	2502247	350mm	250mm	4mm	320 x 200mm	Mild Steel
AMI04030	2502248	400mm	300mm	4mm	370 x 250mm	Mild Steel
AMI04040	2502249	400mm	400mm	4mm	370 x 350mm	Mild Steel
AMI04050	2502250	400mm	500mm	4mm	370 x 450mm	Mild Steel
AMI04060	2502251	400mm	600mm	4mm	370 x 550mm	Mild Steel

Catalog Number	E-Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI05030	2502252	500mm	300mm	4mm	470 x 250mm	Mild Steel
AMI05040	2502253	500mm	400mm	4mm	470 x 350mm	Mild Steel
AMI05050	2502254	500mm	500mm	4mm	470 x 450mm	Mild Steel
AMI06040	2502255	600mm	400mm	4mm	570 x 350mm	Mild Steel
AMI06050	2502256	600mm	500mm	4mm	570 x 450mm	Mild Steel
AMI06060	2502257	600mm	600mm	4mm	570 x 550mm	Mild Steel
AMI06080	2502258	600mm	800mm	4mm	570 x 750mm	Mild Steel
AMI07050	2502259	700mm	500mm	4mm	670 x 450mm	Mild Steel
AMI08040	2502260	800mm	400mm	4mm	770 x 350mm	Mild Steel

Table 2/2

Catalog Number	E-Number	Height	Width	Depth	Panel Size	Enclosure Material
AMI08060	2502261	800mm	600mm	4mm	770 x 550mm	Mild Steel
AMI08080	2502262	800mm	800mm	4mm	770 x 750mm	Mild Steel
AMI10060	2502263	1000mm	600mm	4mm	970 x 550mm	Mild Steel
AMI10080	2502264	1000mm	800mm	4mm	970 x 750mm	Mild Steel
AMI12060	2502265	1200mm	600mm	4mm	1170 x 550mm	Mild Steel
AMI12080	2502266	1200mm	800mm	4mm	1170 x 750mm	Mild Steel

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

