

Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Steel
Finish: Pregalvanized; Polyurethane



SPECIFICATIONS

Table 1/2

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTT2X12		2"	20.3"	28"	3/4"	3.726"
WBTT2X12BA	Black	2"	20.3"	28"	3/4"	3.726"
WBTT2X12WH	White	2"	20.3"	28"	3/4"	3.726"
WBTT2X16		2"	24.3"	32"	3/4"	3.726"
WBTT2X16BA	Black	2"	24.3"	32"	3/4"	3.726"
WBTT2X16WH	White	2"	24.3"	32"	3/4"	3.726"
WBTT2X18		2"	26.3"	34"	3/4"	3.726"

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTT2X18BA	Black	2"	26.3"	34"	3/4"	3.726"
WBTT2X18WH	White	2"	26.3"	34"	3/4"	3.726"
WBTT2X20BA	Black	2"	28.2"	35.9"	3/4"	3.726"
WBTT2X20WH	White	2"	28.2"	35.9"	3/4"	3.726"
WBTT2X24		2"	32.2"	39.9"	3/4"	3.726"
WBTT2X24BA	Black	2"	32.2"	39.9"	3/4"	3.726"
WBTT2X24WH	White	2"	32.2"	39.9"	3/4"	3.726"
WBTT2X4		2"	12 1/2"	20.2"		3.726"
WBTT2X4BA	Black	2"	12 1/2"	20.2"		3.726"
WBTT2X4WH	White	2"	12 1/2"	20.2"		3.726"
WBTT2X6		2"	14.4"	22.1"		3.726"
WBTT2X6BA	Black	2"	14.4"	22.1"		3.726"
WBTT2X6WH	White	2"	14.4"	22.1"		3.726"

Table 2/2

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTT2X8		2"	16.4"	24.1"		3.726"
WBTT2X8BA	Black	2"	16.4"	24.1"		3.726"
WBTT2X8WH	White	2"	16.4"	24.1"		3.726"

Table 1/2

Catalog Number	Unit Weight	Certifications
WBTT2X12	1.235 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X12BA	1.235 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X12WH	1.235 lb	
WBTT2X16	1.646 lb	
WBTT2X16BA	1.646 lb	
WBTT2X16WH	1.646 lb	
WBTT2X18	2.057 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X18BA	2.057 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X18WH	2.057 lb	
WBTT2X20BA	2.675 lb	
WBTT2X20WH	2.675 lb	
WBTT2X24	3.292 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X24BA	3.292 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X24WH	3.292 lb	

Catalog Number	Unit Weight	Certifications
WBTT2X4	0.206 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X4BA	0.206 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X4WH	0.206 lb	
WBTT2X6	0.617 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X6BA	0.617 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X6WH	0.617 lb	

Table 2/2

Catalog Number	Unit Weight	Certifications
WBTT2X8	0.823 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X8BA	0.823 lb	CE, nVent CADDY Wire Basket Tray System
WBTT2X8WH	0.823 lb	

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

