


# Side Panels, SPM



These side panels will ensure that the ingress protection is maintained, which means that the electrical components will operate without any disturbances and protect personnel from injuries.

## FEATURES

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers. Can be replaced by the side door DNS.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: IP 55, TYPE 12, 13 in combination with MCS. IP66, TYPE 4, 12, 13 in combination with MCS-HP.

Pack quantity: 2 panels with mounting accessories.

**Finish:** Powder Coated  
**Color Code:** RAL 7035  
**Thickness:** 16ga

## SPECIFICATIONS

| Catalog Number                                                                                | Article Number | Height  | Width  | Depth   | Color      | Product Family |
|-----------------------------------------------------------------------------------------------|----------------|---------|--------|---------|------------|----------------|
| SPM1805R5  | SPM1805R5      | 69.45in | 0.75in | 18.19in | Light Gray | Free-Standing  |
| SPM1804R5  | SPM1804R5      | 69.45in | 0.75in | 14.25in | Light Gray | Free-Standing  |
| SPM1806R5                                                                                     | SPM1806R5      | 69.45in | 0.75in | 22.13in | Light Gray | Free-Standing  |
| SPM2005R5  | SPM2005R5      | 77.32in | 0.75in | 18.19in | Light Gray | Free-Standing  |
| SPM2004R5                                                                                     | SPM2004R5      | 77.32in | 0.75in | 14.25in | Light Gray | Free-Standing  |
| SPM2006R5  | SPM2006R5      | 77.32in | 0.75in | 22.13in | Light Gray | Free-Standing  |
| SPM2008R5                                                                                     | SPM2008R5      | 77.32in | 0.75in | 30in    | Light Gray | Free-Standing  |
| SPM2206R5                                                                                     | SPM2206R5      | 85.2in  | 0.75in | 22.13in | Light Gray | Free-Standing  |
| SPM2208R5                                                                                     | SPM2208R5      | 85.2in  | 0.75in | 30in    | Light Gray | Free-Standing  |
| SPM1106R5                                                                                     | SPM1106R5      | 41.89in | 0.75in | 22.13in | Light Gray | Free-Standing  |
| SPM1406R5                                                                                     | SPM1406R5      | 53.7in  | 0.75in | 22.13in | Light Gray | Free-Standing  |
| SPM1606R5                                                                                     | SPM1606R5      | 61.57in | 0.75in | 22.13in | Light Gray | Free-Standing  |
| SPM1808R5                                                                                     | SPM1808R5      | 69.45in | 0.75in | 30in    | Light Gray | Free-Standing  |

| Catalog Number | Article Number | Height  | Width  | Depth   | Color      | Product Family |
|----------------|----------------|---------|--------|---------|------------|----------------|
| SPM2010R5      | SPM2010R5      | 78.74in | 0.75in | 39.37in | Light Gray | Free-Standing  |
| SPM1205R5      |                | 47.24in | 0.75in | 19.68in | Light Grey | Free-Standing  |
| SPM1405R5      | 60017          | 53.7in  | 0.75in | 19.68in | Light Gray | Free-Standing  |
| SPM1605R5      | 60018          | 61.57in | 0.75in | 18.19in | Light Gray | Free-Standing  |
| SPM2210R5      |                | 86.61in | 0.75in | 39.37in | Light Gray |                |

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

