

Wide Mounting Plates, MPW



The extra wide mounting plate offers more mounting space and can be fully equipped before being fitted within the enclosure. It can be fitted from the side of the enclosure since, it is wider than the front of enclosure opening.

FEATURES

Description: Creates an installation surface over the full width of the enclosure. Easy installation by use of sliding profiles MTS from the side. Nominal width equals the enclosure width. When combining enclosures the MPWs can be connected and slid in as one installation surface. Can not be mounted in the rearmost position.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece with mounting accessories.

Mounting requirements: Add sliding profiles MTS. MPW fits in combinable enclosures only.

Material: Mild Steel
Finish: Galvanized
Thickness: 11ga

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Enclosure Material
MPW1808	MPW1808	70.87in	31.5in	0.98in	Mild Steel
MPW1810	MPW1810	70.87in	39.37in	0.98in	Mild Steel
MPW1812	MPW1812	70.87in	47.24in	0.98in	Mild Steel
MPW1816	MPW1816	70.87in	63in	0.98in	Mild Steel
MPW2008	MPW2008	78.74in	31.5in	0.98in	Mild Steel
MPW2010	MPW2010	78.74in	39.37in	0.98in	Mild Steel
MPW2012	MPW2012	78.74in	47.24in	0.98in	Mild Steel
MPW2016	MPW2016	78.74in	63in	0.98in	Mild Steel
MPW1805	MPW1805	70.87in	19.69in	0.98in	Mild Steel
MPW1806	MPW1806	70.87in	23.62in	0.98in	Mild Steel
MPW2005	MPW2005	78.74in	19.69in	0.98in	Mild Steel
MPW2006	MPW2006	78.74in	23.62in	0.98in	Mild Steel

ADDITIONAL PRODUCT DETAILS

* 1600 mm wide mounting plates are supplied as two 800 mm wide mounting plates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.