


Wire Basket Tray PreForm 90 degree Elbow, 50 x 450 mm, Black, Pregalvanized

NÚMERO DE CATÁLOGO

WBTR902X18BA



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

CARACTERÍSTICAS

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems



ATRIBUTOS DEL PRODUCTO

Material: Acero

Acabado: Pregalvanizado;Poliuretano

Color: Negro

Altura (H): 50.8 mm

Anchura (W): 665.734 mm


Longitud (L): 665.734mm

Tamaño de taladro (HS): 19.05 mm

Radio (R): 94.64mm

Peso por unidad: 3.175 kg

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221

Opción 1: Atención al
cliente

Opción 2: Soporte técnico

Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500



©2026 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.

Este documento lo ha generado el sistema.

