

Wire Basket Tray Independent Underfloor Support, 457x558mm, Pregalvanized

NÚMERO DE CATÁLOGO

WBTUS18



The nVent CADDY Wire Basket Tray Underfloor Support provides a reliable method for routing wire basket trays beneath the floor with independent structural support. This component is ideal for installations requiring low-voltage cabling to pass under cabinets or equipment.

Engineered for stability and simplicity, the underfloor support system eliminates the need for complex framing. It braces the tray directly beneath raised floors, allowing for clean, unobtrusive cable pathways that preserve floor space and reduce visual clutter. This is especially valuable in data centers, control rooms, and other high-density environments where cable organization and accessibility are critical.

The Support integrates seamlessly with the broader nVent CADDY Wire Basket Tray System, ensuring compatibility with shaped and round wire tray profiles. Its design accommodates standard fasteners and finishes, including pre-galvanized, zinc electroplate, and powder coat options, making it adaptable to a wide range of project specifications.

CARACTERÍSTICAS

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Maintains a fixed and secure distance from the ground to ensure safety and accessibility

Available in a range of sizes to match wire basket tray design

Fixed height ensures a level installation

ATRIBUTOS DEL PRODUCTO

Material: Acero

Acabado: Pregalvanizado

Altura (H): 32 mm

Longitud (L): 1474mm


Longitud 1 (L1): 560.78 mm

Anchura (W): 235 mm

Tamaño de taladro (HS): 14.3 mm

Peso por unidad: 2.404 kg

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221

Opción 1: Atención al
cliente

Opción 2: Soporte técnico

Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500



©2026 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.

Este documento lo ha generado el sistema.

