

Kit de paquete de control de agua LHX+

NÚMERO DE CATÁLOGO

23130-663



Los insertos de tubería de acero inoxidable con ID 1" cada uno viene con un par de sensores de refrigerante líquido ratiométrico. Los sensores se conectan directamente al controlador de puerta trasera RackChiller. Esto permite monitorear las propiedades térmicas del refrigerante y el rendimiento de la refrigeración, así como funciones adicionales de control de temperatura.

CARACTERÍSTICAS

Sensores de retorno: Flujo de refrigerante y temperaturas

Permite al controlador modular el flujo basado en la temperatura de retorno

Unidad de control de agua con flujo de agua, sensor de temperatura

Ambas inserciones de tubería hechas de acero inoxidable que se pueden atornillar a la placa base para asegurar un alto EMC e IP

Ambos insertos de tubería fabricados en acero inoxidable que pueden ser atornillados a la placa base para garantizar altos niveles de EMC y IP

ATRIBUTOS DEL PRODUCTO

Tipo de producto: Kit de conector

Compatible con: Varistar; Varistar CP

Peso bruto: 0.576kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Controlador LHX+ requerido.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE