

nVent LENTON Interlok Form Saver Seal

The nVent LENTON Interlok Form Saver Seal provides an easy and efficient means for securing nVent LENTON Interlok Grout-Fill Coupler variants to formwork. Designed for cast-in-place applications, simply click and tap the Form Saver Seal into the coupler and utilize the sturdy mounting plate to fasten onto the formwork. The integrated seal allows the secondary rebar to be inserted into the coupler and prevents concrete paste contamination and grout leakage out of the cavity.

Interlok Grout-Fill Coupler variants can be used to splice steel bars in various cast-in-place applications. When combined with the Form Saver Seal, this powerful combination can be utilized for segmental pours, closure pours, post-tensioned slabs, and repair work.

FONCTIONS

Sturdy, spring-steel mounting flange

Integrated rubber seal for grout cavity

Easy snap-in installation

Four keyholes for easy fastening using nails/screws

Anchor tabs prevent dislodging in concrete

Compatible with all nVent LENTON Interlok Grout-Fill Coupler variants

Finition: Brut

Matériau: Acier

SPÉCIFICATIONS

Référence catalogue	Longueur (L)	Largeur (W)	Hauteur (H)	A	Couleur	Poids unitaire	Quantité par colis
LKFSA20	101.6mm	113.6mm	10.2mm	85.2 mm	Jaune	0.1 kg	50
LKFSA25	101.6mm	113.6mm	10.2mm	85.2 mm	Rouge	0.1 kg	50
LKFSA22	101.6mm	113.6mm	10.2mm	85.2 mm	Bleu	0.1 kg	50
LKFSA16	101.6mm	113.6mm	10.2mm	85.2 mm	Noir	0.1 kg	50

Accessory Part Number	Compatible With:	
	Interlok Standard Grout Filled Couplers(LK Series)	Interlok No-Thread Grout Filled Couplers(LKNT Series)
LKFSA16	LK16, LK16D	-
LKFSA20	LK20(D)	LKNT20(D)
LKFSA22	LK5, LK6, LK7, LK22(D)	LKNT22(D)
LKFSA25	LK8, LK25(D)	LKNT25(D)

DIAGRAMMES

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221
Option 1 – Service client
Option 2 – Assistance
technique

Europe

Pays-Bas :
+31 800-0200135
France :
+33 800 901 793

Europe

Allemagne :
800 1890272
Autres pays :
+31 13 5835404

APAC

Shanghai :
+ 86 21 2412 1618/19
Sydney :
+61 2 9751 8500



Notre portefeuille puissant de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE