

# Wire Basket Tray L Bracket, 200 mm, Black, Electrogalvanized

## RÉFÉRENCE CATALOGUE

### WBTLBRKT8BA



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

## FONCTIONS

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs



## ATTRIBUTS DU PRODUIT

Matériau: Acier

Finition: Électro-galvanisé

Couleur: Noir

Hauteur (H): 127 mm


Largeur (W): 41.4 mm

Longueur (L): 553.72mm

Taille de trou (HS): 7.16 mm

Poids unitaire: 0.553 kg

## DIAGRAMMES



## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Toutes les marques et tous les logos nVent sont la propriété ou sont sous licence de nVent Services GmbH ou de ses sociétés affiliées. Toutes les autres marques déposées sont la propriété de leurs détenteurs respectifs. nVent se réserve le droit de modifier les spécifications sans préavis.

Ce document est généré par le système.

