

Kit di schermatura in tessuto EMC sul pannello anteriore, -40... +70°C, 6 U; 100 pezzi

CODICE A CATALOGO

21101-856


Le guarnizioni EMC in tessuto sono inserite in una fessura sul lato destro dei pannelli anteriori a U. Le guarnizioni sono incollate al pannello anteriore.

CARATTERISTICHE

La guarnizione EMC in tessuto è applicata lateralmente sul pannello anteriore o nella scanalatura del profilo destro, a seconda dei casi.

La guarnizione del profilo è incollata sulla superficie di contatto della staffa da 19" o dell'angolo posteriore e imposta il collegamento conduttivo ai pannelli anteriori a forma di U

Range di temperatura -40 °C ... +70 °C.



ATTRIBUTI DEL PRODOTTO

Altezza del rack: 6U

Quantità nella confezione: 100

Profondità (D): 1.62mm

Altezza (H): 232mm

Materiale: Elastomero termoplastico

Famiglia di prodotti: EuropacPRO; RatiopacPRO; RatiopacPRO air; PropacPRO; Unità a innesto di tipo profilato

Tipo di prodotto: Kit di schermatura

Larghezza (W): 3.8mm

Funziona con: Rack secondari; Custodie; Pannelli frontali

Classificazione dell'infiammabilità: UL® 94V-0

Peso lordo: 0.174kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on

SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Le guarnizioni EMC (in tessuto) sono necessarie per schermare i pannelli anteriori.

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE