

Modulo di riempimento MTCA.4 con deflettore aria, di medie dimensioni, doppio

CODICE A CATALOGO

21850-106

Per coprire gli slot AdvancedMC, MCH o PM inutilizzati nei sistemi MTCA.1 e MTCA.4 o gli slot inutilizzati in un sistema MTCA.0 con barra di bloccaggio. I moduli sono costituiti da un pannello anteriore con fermi e viti prigioniere, guarnizione EMC e pannello laterale. I moduli possono essere fissati all'alloggiamento della scheda con le viti prigioniere.

CARATTERISTICHE

Conforme alle specifiche MicroTCA.1 e MicroTCA.4

Per coprire gli slot inutilizzati all'interno di un sistema MicroTCA.1 o MicroTCA.4

Flange con viti prigioniere M3 per il fissaggio alla gabbia della scheda

Schermatura EMC



ATTRIBUTI DEL PRODOTTO

Funzione di progettazione: Di medie dimensioni

Quantità nella confezione: 1

Materiale: Acciaio inossidabile

Famiglia di prodotti: MicroTCA

Tipo di prodotto: Modulo di sistema

Tipo: Modulo di riempimento

Peso netto: 0.35kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE