

Printplaathouder C

CATALOGUSNUMMER

24560-377

Met de PCB-hendel kan een gebruiker een printplaat verwijderen zonder voorpaneel.

KENMERKEN

Mogelijke toepassing op de bovenste en onderste horizontale rail



Kan ook worden gebruikt zonder PCB-handgreep

Kan ook worden gebruikt vanuit sleuf positie „2”

Voor het bevestigen van printplaten in een subrack- of 19-inch behuizing

Voor EuropacPRO, MultipacPRO, RatiopacPRO, PropacPRO en CompacPRO

Kan alleen gebruikt worden in combinatie met geleiderails type ?accessoire?



PRODUCTKENMERKEN

Producttype: PCB-houder

Materiaal: Polycarbonaat

Hoeveelheid in verpakking: 10

Nettogewicht: 0.017kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AANVULLENDE PRODUCTGEGEVENS

Bestel handvat C afzonderlijk.

Kan alleen worden gebruikt met geleiderail-accessoire.

Minimale afstand van de geleiderail: 3 PK.

Kan niet worden gebruikt in combinatie met Propac, Compac of Inpac gevallen.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

