

Wire Basket Tray L Bracket, 6", Black, Electrogalvanized

RÉFÉRENCE CATALOGUE

WBTLBRKT6BA



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

FONCTIONS

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs



ATTRIBUTS DU PRODUIT

Matériau: Acier

Finition: Électro-galvanisé

Couleur: Noir

Hauteur (H): 127 mm


Largeur (W): 41.4 mm

Longueur (L): 502.92mm

Taille de trou (HS): 7.16 mm

Poids unitaire: 0.476 kg

DIAGRAMMES



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221

Option 1 – Service client

Option 2 – Assistance

technique

Europe

Pays-Bas :

+31 800-0200135

France :

+33 800 901 793

Europe

Allemagne :

800 1890272

Autres pays :

+31 13 5835404

APAC

Shanghai :

+ 86 21 2412 1618/19

Sydney :

+61 2 9751 8500



©2026 nVent. Toutes les marques de commerce et logos de nVent sont la propriété de nVent Services GmbH ou de ses filiales. Toutes les autres marques de commerce sont la propriété de leurs propriétaires respectifs. nVent se réserve le droit de modifier les spécifications sans préavis.

Ce document est généré automatiquement par le système.

nVent.com/ENDDT

