

Wire Basket Tray Ceiling Support, 150 mm, Pregalvanized

KATALOGNUMMER

WBTCLSPRT6



In the evolving landscape of cable management, the nVent CADDY Wire Basket Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FUNKSJONER

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY Wire Basket Tray Ground Splice and nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod



PRODUKTEGENSKAPER

Materiale: Stål

Overflate: Forhåndsgalvanisert

Høyde (H): 15.75 mm


Bredde (W): 41.4 mm

Lengde (L): 238.404mm

Hullstørrelse (HS): 13.49 mm

Enhetsvekt: 0.249 kg

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

Nord-Amerika

+1.800.753.9221

Alternativ 1 –

Kundeservice

Alternativ 2 – Teknisk

støtte

Europa

Nederland:

+31 800-0200135

Frankrike:

+33 800 901 793

Europa

Tyskland:

800 1890272

Andre land:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Alle nVent-merker og -logoer er eid eller lisensiert av nVent Services GmbH eller dets datterselskaper. Alle andre varemerker eies av de respektive eierne. nVent forbeholder seg retten til å endre spesifikasjonene uten forvarsel.

Dette dokumentet er systemgenerert.

nVent.com/ENDDT

