

Digital kontaktsensor (inngang) med 12 V-tilførsel for Guardian Management Gateway

KATALOGNUMMER

21070-125

Ekstern sensor overvåker digitale innganger/utganger med 2 RJ45-kontakter. Opptil 16 sensorer kan kobles til én Guardian Management Port.



FUNKSJONER

Ekstern sensor for Guardian Management Gateway

En port er i stand til å overvåke opptil 16 sensorenheter med en total kabellengde på 40 meter

Hvis en nVent SCHROFF Guardian-sensor er tilkoblet, vises den i nettgrensesnittet med type og serienummer

Metallhus

Enkel montering

2 x RJ 45-tilkobling

Enkel Daisy chain med CAT6 patch kabel (eller høyere skjerming)

PRODUKTEGENSKAPER

Produkttype: Føler

Type: Digital kontakt

Fungerer med: Gateway for styring av veileder

Bruttovekt: 0.097kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

