

Wire Basket Tray L Bracket, 300 mm, Black, Electrogalvanized

CODICE A CATALOGO

WBTLBRKT12BA



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

CARATTERISTICHE

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs



ATTRIBUTI DEL PRODOTTO

Materiale: Acciaio

Finitura: Elettrozincato

Colore: Nero

Altezza (H): 127 mm


Larghezza (W): 41.4 mm

Lunghezza (L): 198.12mm

Dimensione del foro (HS): 7.16 mm

Peso unitario: 0.712 kg

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Tutti i marchi e i loghi nVent sono di proprietà o concessi in licenza da nVent Services GmbH o dalle sue affiliate. Tutti gli altri marchi sono di proprietà dei rispettivi proprietari. nVent si riserva il diritto di modificare le specifiche senza preavviso.

Questo documento è generato dal sistema.

nVent.com/ENDDT

