

Wire Basket Tray Independent Underfloor Support, 101x558mm, Pregalvanized

CODICE A CATALOGO

WBTUS04



The nVent CADDY Wire Basket Tray Underfloor Support provides a reliable method for routing wire basket trays beneath the floor with independent structural support. This component is ideal for installations requiring low-voltage cabling to pass under cabinets or equipment.

Engineered for stability and simplicity, the underfloor support system eliminates the need for complex framing. It braces the tray directly beneath raised floors, allowing for clean, unobtrusive cable pathways that preserve floor space and reduce visual clutter. This is especially valuable in data centers, control rooms, and other high-density environments where cable organization and accessibility are critical.

The Support integrates seamlessly with the broader nVent CADDY Wire Basket Tray System, ensuring compatibility with shaped and round wire tray profiles. Its design accommodates standard fasteners and finishes, including pre-galvanized, zinc electroplate, and powder coat options, making it adaptable to a wide range of project specifications.

CARATTERISTICHE

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Maintains a fixed and secure distance from the ground to ensure safety and accessibility

Available in a range of sizes to match wire basket tray design

Fixed height ensures a level installation

ATTRIBUTI DEL PRODOTTO

Materiale: Acciaio

Finitura: Prezincato

Altezza (H): 32 mm

Lunghezza (L): 767mm


Lunghezza 1 (L1): 560.78 mm

Larghezza (W): 235 mm

Dimensione del foro (HS): 14.3 mm

Peso unitario: 0.862 kg

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Tutti i marchi e i loghi nVent sono di proprietà o concessi in licenza da nVent Services GmbH o dalle sue affiliate. Tutti gli altri marchi sono di proprietà dei rispettivi proprietari. nVent si riserva il diritto di modificare le specifiche senza preavviso.

Questo documento è generato dal sistema.

nVent.com/GRDD1

