

# nVent CADDY Ladder Tray Clip

The nVent CADDY Ladder Tray Clip makes attaching ladder trays to strut profiles quick and easy—featuring a single-piece design, ready for use out-of-the box with no loose hardware.

Offering two simple installation methods, the Ladder Tray Clip can be either installed on top of the strut or slid in from either end of the channel, increasing flexibility and giving contractors more options on the job. Designed for both indoor and outdoor installations, the hot-dip galvanized finish and hardware ensure longevity on rooftop, solar and trapeze projects.

## FUNKCJE

Single-piece design with hardware pre-installed to reduce components

Simple and time-saving; just drop and twist the Ladder Tray Clip directly into the strut profile

Works on ladder tray with up to ½ in flange thickness

Hot-dip galvanized clamp and hardware for demanding environments

Integrated clamping teeth for superior holding strength and load ratings



## SPECYFIKACJE

Table 1/2

| Numer katalogowy | Materiał | Wykończenie       | Grubość kołnierza (FT) | A.    | B.      | Moment obrotowy (TQ) |
|------------------|----------|-------------------|------------------------|-------|---------|----------------------|
| LTC              | Stal     | Cynkowane ogniowo | 13 mm Max              | 49 mm | 38.1 mm | 41 N·m               |

Table 2/2

| Numer katalogowy | Ostateczne obciążenie statyczne 1 (F1) | Ostateczne obciążenie statyczne 2 (F2) | Ostateczne obciążenie statyczne 3 (F3) |
|------------------|----------------------------------------|----------------------------------------|----------------------------------------|
| LTC              | 2225N                                  | 3100N                                  | 10675N                                 |



## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

### Ameryka Północna

+1.800.753.9221

Opcja 1 – obsługa klienta

Opcja 2 – wsparcie

techniczne

### Europa

Niderlandy:

+31 800-0200135

Francja:

+33 800 901 793

### Europa

Niemcy:

800 1890272

Inne kraje:

+31 13 5835404

### APAC

Szanghaj:

+ 86 21 2412 1618/19

Sydney:

+61 2 975 185 00



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

