

# Wire Basket Tray Drop Out



The nVent CADDY Wire Basket Tray Drop Out is a versatile solution for creating cable management exits in cable tray. By acting as a wire funnel, the Drop Out enables cables to easily drop vertically from the tray while ensuring proper support and protecting the bend radius at the exit point. The tool-free design allows installers to drop the component into place on the wire basket tray while the side prongs hold it firmly in place. Whether contractors are working with multi-tier assemblies or side-by-side configurations, the Drop Out offers an aesthetic and efficient way to manage cable transitions, without compromising on performance or accessibility.

## FUNKCJE

Designed for center cable tray dropouts

Conducive to creating both multi-tier tray and side-by-side assemblies

Easily cut to fit around the wire basket tray for retrograde cable installations

Ensures the natural bend radius of the cable is protected

Stackable for multiple adjoining dropouts



Reusable and tool-free—easy-to-install, easy-to-remove

**Materiał:** ABS, klasa UL-V0

**Wykończenie:** Wstępnie galwanizowane

## SPECYFIKACJE

| Numer katalogowy | Wysokość (H) | Szerokość (W) | Długość (L) | Masa urządzenia |
|------------------|--------------|---------------|-------------|-----------------|
| WBTCBLDO         | 28.6 mm      | 58.74 mm      | 90.5mm      | 0.05 kg         |
| WBTCBLDO4        | 28.6 mm      | 109.3 mm      | 92.08mm     | 0.01 kg         |
| WBTCBLDO6        | 29.4 mm      | 158 mm        | 210.85mm    | 0.02 kg         |



## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

### Ameryka Północna

+1.800.753.9221

Opcja 1 — obsługa klienta

Opcja 2 — wsparcie

techniczne

### Europa

Niderlandy:

+31 800-0200135

Francja:

+33 800 901 793

### Europa

Niemcy:

800 1890272

Inne kraje:

+31 13 5835404

### APAC

Szanghaj:

+ 86 21 2412 1618/19

Sydney:

+61 2 975 185 00

