


Telescop. beugel, 400–635mm t.b.v. elek.dzn gipswanden, inbwdpte 38, 54, 63,5mm

CATALOGUSNUMMER

TSGB1624



The nVent CADDY Telescoping Screw Gun Box Bracket, First Means is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers both traditional and retrofit mounting, which allows the bracket to bend for multiple depths and mount from both the front and back of the stud—making it ideal for when drywall has already been installed. As the first means of support, conduit can be run directly to the electrical box while ensuring a smooth, flat drywall finish with side-mount installations. The notched and clearly marked bend points make installation safe, fast and easy.

KENMERKEN

Designed for both single and multiple box mounting

Unique single-component break-apart design

Stamped inch markings and pilot holes accelerate precise box conduit mounting

Pilot holes allow for easy access with a screwdriver

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly



PRODUCTKENMERKEN

Artikelnummer: 187199

Materiaal: Staal

Afwerking: Voorgegalvaniseerd

Afstand tussen tapeinden: 400 - 635 mm

Diepte doos: 38mm;54mm;63.5mm

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221
optie 1 – Klantenservice
optie 2 – Technische
ondersteuning

Europa

Nederland:
+31 800-0200135
Frankrijk:
+33 800 901 793

Europa

Duitsland:
800 1890272
andere landen:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. Alle nVent-merken en -logo's zijn eigendom van of in licentie gegeven door nVent Services GmbH of haar gelieerde ondernemingen. Alle andere handelsmerken zijn het eigendom van hun respectieve eigenaren. nVent behoudt zich het recht voor om specificaties zonder kennisgeving te wijzigen.

Dit document is door het systeem gegenereerd.

