


Panel przedni Zestaw ekranujący ze stali nierdzewnej EMC, 6 U, 100 sztuk



NUMER KATALOGOWY

21101-708

Uszczelki EMC ze stali nierdzewnej są umieszczane w bocznych szczelinach osłoniętych paneli przednich (2 sztuk na panel przedni).

FUNKCJE

Uszczelki EMC ze stali nierdzewnej są umieszczane w bocznych szczelinach osłoniętych paneli przednich (2 sztuk na panel przedni)

Taśma kontaktowa EMC, stal nierdzewna

Zakres temperatur -200 °C ... +160 °C.



ATRYBUTY PRODUKTU

Wysokość stojaka: 6U

Liczba opakowań: 100

Materiał: Stal nierdzewna

Rodzina produktów: EuropacPRO; RatiopacPRO; RatiopacPRO air; PropacPRO; Moduł wtykowy typu ramowego


Typ produktu: Zestaw ekranujący

Współpracuje z: Stojaki podrzędne; Obudowy; Panele przednie

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Proszę zamówić narzędzie montażowe oddzielnie.



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE