


Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

KENMERKEN

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Materiaal: Staal
Afwerking: Voorgegalvaniseerd;Polyurethaan



SPECIFICATIES

Table 1/2


Catalogusnummer	Kleur	Hoogte (H)	Breedte (W)	Lengte (L)	Gatgrootte (HS)	Radius (R)
WBTI2X12		50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X12BA	Zwart	50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X18		50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X18BA	Zwart	50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X24		50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X24BA	Zwart	50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X4		50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X4BA	Zwart	50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X6		50.8 mm	561.34 mm	561.34mm		94.64mm

Catalogusnummer	Kleur	Hoogte (H)	Breedte (W)	Lengte (L)	Gatgrootte (HS)	Radius (R)
WBTI2X6BA	Zwart	50.8 mm	561.34 mm	561.34mm		94.64mm
WBTI2X8		50.8 mm	612.14 mm	612.14mm		94.64mm
WBTI2X8BA	Zwart	50.8 mm	612.14 mm	612.14mm		94.64mm

Table 2/2

Catalogusnummer	Gewicht eenheid	Certificeringen
WBTI2X12	3.175 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X12BA	3.175 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X18	5.443 kg	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X18BA	5.443 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X24	8.165 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X24BA	8.165 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X4	0.907 kg	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X4BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X6	1.361 kg	cUL, CE, nVent CADDY Wire Basket Tray System, UL
WBTI2X6BA	1.361 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X8	2.268 kg	UL, cUL, CE, nVent CADDY Wire Basket Tray System
WBTI2X8BA	2.268 kg	CE, nVent CADDY Wire Basket Tray System

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

Noord-Amerika

+1.800.753.9221

optie 1 – Klantenservice

optie 2 – Technische
ondersteuning

Europa

Nederland:

+31 800-0200135

Frankrijk:

+33 800 901 793

Europa

Duitsland:

800 1890272

andere landen:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

