


Krageskrue, Cross Recess/Slottet



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

FUNKSJONER

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

Produkttype: Skrue

Type: Skrue



SPESIFIKASJONER

Table 1/3

Katalognummer	Diameter	Lengde	Materiale	Overflate	Antall pakker	Gjengestørrelse
21101-101		12.3mm	Stål	Nikkelbelagt	100	M2.5
21101-906		12.3mm	Rustfritt stål		100	M2.5
21101-102		12.3mm	Stål	Zinc Plated, Black	100	M2.5
21101-323		11mm			100	M2.5
21102-026	2.5mm	12.3mm	Stål	Nikkelbelagt	100	M2.5

Table 2/3

Katalognummer	Dybde	Høyde	Bredde	Fungerer med	Gjengelengde	Gjengetype
21101-101	14.3mm	5mm	5mm	Frontpaneler	12.3mm	Metrisk
21101-906				Frontpaneler	12.3mm	
21101-102	14.3mm	5mm	5mm	Frontpaneler	12.3mm	Metrisk
21101-323				Frontpaneler		
21102-026				Rammetype, pluggbar enhet, Kassetter	3mm	

Table 3/3

Katalognummer	Dreiemoment	Sertifiseringer
21101-101	0.3N·m	RoHS
21101-906	0.3N·m	RoHS
21101-102	0.3N·m	RoHS
21101-323	0.3N·m	
21102-026	0.3N·m	

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

