


MicroTCA.4 frontpanel (over MCH), middels størrelse enkelt, skjermet, SST



KATALOGNUMMER

21850-102

AdvancedTCA frontpanel (rustfritt stål) for tekstilpakninger. Skjermede fyllmoduler brukes til å lukke ubrukte spor.

FUNKSJONER

I henhold til MicroTCA.1 og MicroTCA.4 spesifikasjoner

Skjermede fyllmoduler brukes til å lukke ubrukte spor

Kan skrus på. Støttes på styreskinnen



PRODUKTEGENSKAPER

Høyde: 84.68mm

Antall pakker: 1

Tilbehørstype: Frontpanel

Montering: Front som skrus på

Pakning: Tekstil

Fremre overflate: Rå

Bakre flate: Rå

Dybde: 1mm

EMC-beskyttelse: Ja

Materiale: Rustfritt stål

Produktserie: AdvancedMC

Produkttype: Frontpanel

Type: Frontpanel

Bredde: 18.96mm

Bruttovekt: 0.047kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

