

Wire Basket Tray L Bracket



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

CARACTERÍSTICAS

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs


Material: Aço
Acabamento: Electrogalvanized



ESPECIFICAÇÕES

Número de catálogo	Cor	Altura (H)	Largura (W)	Length (L)	Tamanho do orifício (HS)	Peso unitário
WBTLBRKT12		127 mm	41.4 mm	350.52mm	7.16 mm	0.712 kg
WBTLBRKT12BA	Black	127 mm	41.4 mm	198.12mm	7.16 mm	0.712 kg
WBTLBRKT4		127 mm	41.4 mm	96.52mm	7.16 mm	0.395 kg
WBTLBRKT4BA	Black	127 mm	41.4 mm	452.12mm	7.16 mm	0.395 kg
WBTLBRKT6		127 mm	41.4 mm	452.12mm	7.16 mm	0.476 kg
WBTLBRKT6BA	Black	127 mm	41.4 mm	502.92mm	7.16 mm	0.476 kg
WBTLBRKT8		127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg
WBTLBRKT8BA	Black	127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

