

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CARACTERÍSTICAS

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

Acabamento: Chapa de Aço Zincada

Product Type: Assembly Kit



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Length	Quantidade por embalagem	Tamanho da rosca	Material	Família de produtos	Tipo
21101-809		50	M6	Aço, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21101-810		100	M6	Aço, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21100-435		8	M6	Aço, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21190-435		32	M6	Aço, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit

Número de catálogo	Length	Quantidade por embalagem	Tamanho da rosca	Material	Família de produtos	Tipo
21190-095		4	M6	Aço, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit
21120-196	16mm	4	M6	Aço		Mounting Kit, Grounding
21120-197	16mm	32	M6	Aço		Mounting Kit, Grounding
21120-198	16mm	50	M6	Aço		Mounting Kit, Grounding
21120-199	13mm	100	M6	Aço		Mounting Kit, Grounding
21120-213		4	M6	Aço		Mounting Kit
21120-214		50	M6	Aço		Mounting Kit
21120-215		32	M6	Aço		Mounting Kit
21120-216		100	M6	Aço		Mounting Kit

Table 2/2		
Número de catálogo	Works With	Certifications
21101-809	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21101-810	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21100-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21190-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21190-095	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-196	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-197	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-198	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-199	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-213	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-214	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-215	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	

Número de catálogo	Works With	Certifications
21120-216	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

