

Uchwyt do drabinki do profilów strut, stal ocynkowana ogniowo

NUMER KATALOGOWY

LTC

The nVent CADDY Ladder Tray Clip makes attaching ladder trays to strut profiles quick and easy—featuring a single-piece design, ready for use out-of-the box with no loose hardware.

Offering two simple installation methods, the Ladder Tray Clip can be either installed on top of the strut or slid in from either end of the channel, increasing flexibility and giving contractors more options on the job. Designed for both indoor and outdoor installations, the hot-dip galvanized finish and hardware ensure longevity on rooftop, solar and trapeze projects.

FUNKCJE


Single-piece design with hardware pre-installed to reduce components

Simple and time-saving; just drop and twist the Ladder Tray Clip directly into the strut profile

Works on ladder tray with up to ½ in flange thickness

Hot-dip galvanized clamp and hardware for demanding environments

Integrated clamping teeth for superior holding strength and load ratings



ATRYBUTY PRODUKTU

Numer artykułu: 387715

Materiał: Stal

Wykończenie: Cynkowane ogniowo

Grubość kołnierza (FT): 13 mm Max

A.: 49 mm

B.: 38.1 mm

Średnica wkrętu (Sc): 3/8"



Moment obrotowy (TQ): 41 N·m

Ostateczne obciążenie statyczne 1 (F1): 2225N

Ostateczne obciążenie statyczne 2 (F2): 3100N

Ostateczne obciążenie statyczne 3 (F3): 10675N

SCHEMATY



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

Ameryka Północna

+1.800.753.9221

Opcja 1 — obsługa klienta

Opcja 2 — wsparcie

techniczne

Europa

Niderlandy:

+31 800-0200135

Francja:

+33 800 901 793

Europa

Niemcy:

800 1890272

Inne kraje:

+31 13 5835404

APAC

Szanghaj:

+ 86 21 2412 1618/19

Sydney:

+61 2 975 185 00



©2026 nVent. Wszystkie znaki i logo nVent są własnością firmy nVent Services GmbH albo jej spółek zależnych lub są licencjonowane. Wszystkie pozostałe znaki towarowe są własnością odpowiednich właścicieli. Firma nVent zastrzega sobie prawo do zmiany specyfikacji bez powiadomienia.

Ten dokument jest generowany przez system.

