


Front Panel EMC Stainless Steel Shielding Kit



The stainless steel EMC gaskets are inserted into the lateral slots of the shieldable front panels (2 pieces per front panel).

CARACTERÍSTICAS

The stainless steel EMC gaskets are inserted into the lateral slots of the shieldable front panels (2 pieces per front panel)

EMC contact strip, stainless steel

Temperature range -200 °C ... +160 °C

Material:	Aço inoxidável
Família de produtos:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; PropacPRO; Frame Type Plug-In Unit
Product Type:	Shielding Kit
Works With:	Subracks; Cases; Front Panels




ESPECIFICAÇÕES

Número de catálogo	Rack Height	Quantidade por embalagem	Profundidade (D)	Altura (H)	Largura (W)
21101-705	3U	10	2.22mm	97mm	4.97mm
21101-707	6U	10	2.22mm		4.97mm
21101-706	3U	100	2.22mm	97mm	4.97mm
21101-708	6U	100			
21101-709	9U	10	2.22mm		4.97mm
21101-710	9U	100			
21101-713	4U	10	2.22mm	142mm	4.97mm
21101-714	4U	100			
21101-775	2U	10	2.22mm	52mm	4.97mm
21101-776	2U	100			
21101-777	5U	10			
21101-778	5U	100			

DETALHES ADICIONAIS DO PRODUTO

Please order assembly tool separately.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

