


Plug-In Unit Kit for PMC, Chromated, Shielded (Textile) With Handle



U-shaped front panel with cutout for PMC. Shieldable for textile EMC gasket.

CARACTERÍSTICAS

In accordance with IEEE P1386, PCI Mezzanine Card

For single 69.0 x 76.5 mm or double 139.0 x 76.5 mm modules

For standard defined I/O mezzanine modules which connect to carrier cards

PMC = PCI Mezzanine Card

FPGA = Field Programmable Gate Array

U-profile front panel 3 U, 4 HP, with textile gasketing

EMC shielding for front panel and coverings for front panel cutouts

EMC Shielding:	Sim
Material:	Aluminio
Product Type:	Front Panel
Rack Width:	4HP
Tipo:	Front Panel with Handle (PIU)

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Quantidade por embalagem	Tipo de alça	Instalação	Gasket Type	Front Finish
20836-460	3U	1	IEL	Screw-on Front	Textile EMC	Anodized
20836-461	6U	1	IEL	Screw-on Front	Textile EMC	Anodized

Table 2/2

Número de catálogo	Rear Finish	Em conformidade com	Acabamento
20836-460	Conductive	PMC Mezzanine, IEEE P1386	Anodized, Passivated
20836-461	Conductive	PMC Mezzanine, IEEE P1386	Anodized, Passivated

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

