


Panel przedni termostatu z wyświetlaczem cyfrowym, 19 U, 2.5 mm, Al, RAL 7021



NUMER KATALOGOWY

30118-360

Panel przedni termostatu z wyświetlaczem cyfrowym 19U.

FUNKCJE

Panel przedni 19U, z wycięciem dla termostatu z wyświetlaczem cyfrowym



ATRYBUTY PRODUKTU

Typ produktu: Panel przedni

Typ: Panel przedni 19"

Typ akcesorium: Panel przedni

Montaż: Przykręcany przód

Ekranowanie EMC: Nie

Materiał: Aluminium

Wykończenie z przodu: Malowane

Wykończenie z tyłu: Malowane

Kod koloru: RAL 7021

Wysokość stojaka: 1U

Wysokość: 43mm

Szerokość stojaka: 95HP

Szerokość: 483mm

Głębokość: 3mm

Liczba opakowań: 1

Wykończenie: Powłoka proszkowa

Waga brutto: 0.109kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE