


EuropacPRO Cover Plate, Universal



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be used is non-standard boards will be assembled into the subrack.

CARACTERISTICAS

Shielding is provided by optional EMC stainless steel gaskets, between cover plate and side panel

For variable positioning of horizontal rails e.g. for PCBs with non-standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

Material:	Aluminio
Product Type:	Cover Plate
Família de produtos:	EuropacPRO
Acabamento:	Passivated
Works With:	Subracks
Tipo:	Universal



ESPECIFICAÇÕES

Número de catálogo	Rack Width	Profundidade	Quantidade por embalagem	Unidade de embalagem
24560-041	63HP	175mm	2	Pair
24560-031	42HP	175mm	2	Pair
24560-056	84HP	475mm	2	Pair
24560-033	42HP	295mm	2	Pair
24560-055	84HP	415mm	2	Pair
24560-042	63HP	235mm	2	Pair
24560-054	84HP	355mm	2	Pair
24560-053	84HP	295mm	2	Pair
24560-043	63HP	295mm	2	Pair
24560-051	84HP	175mm	2	Pair
24560-032	42HP	235mm	2	Pair

Número de catálogo	Rack Width	Profundidade	Quantidade por embalagem	Unidade de embalagem
24560-052	84HP	235mm	2	Pair

DETALHES ADICIONAIS DO PRODUTO

In addition, 4 contact strips per subrack are required to affix cover to horizontal rail.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE