


# Guide Rail Multi Piece, Mid-Piece Aluminium/Plastic Extrusion



Guide rail mid-piece for individual multi-piece guide rails out of plastic or Aluminum extrusion. Suitable for Standard, Accessory, 4.4" PCB types and end pieces with coding.

## CARACTERISTICAS

Middle profile for mounting guide rails for 2 mm groove width

2 plastic end pieces are required; these are pushed on to both ends of the middle profile

Guide rails can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Storage temperature: from -40 °C ... 130 °C

**Família de produtos:** EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac  
**Product Type:** Guide Rail  
**Tipo:** Middle Section



## ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Material | Cor    | Quantidade por embalagem | Board Depth | Groove Width | Código de cor |
|--------------------|----------|--------|--------------------------|-------------|--------------|---------------|
| 34560-891          | Aluminio | Silver | 1                        | 160mm       | 2            |               |
| 34560-893          | Aluminio | Silver | 1                        | 280mm       | 2            |               |
| 34564-891          | PVC      | Grey   | 1                        | 160mm       | 2            | RAL 7035      |
| 34564-893          | PVC      | Grey   | 1                        | 280mm       | 2            | RAL 7035      |
| 34564-900          | PVC      | Grey   | 1                        | 1000mm      | 2            | RAL 7035      |
| 34564-892          | PVC      | Grey   | 1                        | 220mm       | 2            | RAL 7035      |
| 34560-900          | Aluminio | Silver | 1                        | 1000mm      | 2            |               |
| 34560-892          | Aluminio | Silver | 1                        | 220mm       | 2            |               |

Table 2/2

| Número de catálogo | Acabamento | Works With               |
|--------------------|------------|--------------------------|
| 34560-891          | Anodized   | Subracks, Cases, Chassis |
| 34560-893          | Anodized   | Subracks, Cases, Chassis |
| 34564-891          |            | Subracks, Cases, Chassis |
| 34564-893          |            | Subracks, Cases, Chassis |
| 34564-900          |            | Subracks, Cases, Chassis |
| 34564-892          |            | Subracks, Cases, Chassis |
| 34560-900          | Anodized   | Subracks, Cases, Chassis |
| 34560-892          | Anodized   | Subracks, Cases, Chassis |

## DETALHES ADICIONAIS DO PRODUTO

Delivery may be in Standard Pack Quantity (SPQ). Pricing is per individual item.

One guide rail consists of 1 pair of head pieces and 1 profile piece.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**