

PMC Mezzanine Front Panel, Non-Shielded



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments.

CARACTERÍSTICAS

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring



ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Tipo	Accessory Type	Instalação	EMC Shielding	Gasket Type	Material
20835-899	Mezzanine Front Panel	Front panel	Snapped in	No (Retrofittable)	O-Ring EMC	Alumínio
20835-896	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc
20835-929	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc
20835-931	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc

Table 2/3

Número de catálogo	Front Finish	Rear Finish	Treated Edges	Altura	Largura	Em conformidade com
20835-899	Anodized	Conductive	Sim	74mm	12.7mm	PMC Mezzanine, IEEE P1386
20835-896	Anodized	Anodized	Não	74mm	12.7mm	PMC Mezzanine, IEEE P1386
20835-929	Chrome Plated	Chrome Plated	Sim	74mm	12.7mm	PMC Mezzanine, IEEE P1386
20835-931	Anodized	Conductive	Não	74mm	12.7mm	PMC Mezzanine, IEEE P1386

Table 3/3

Número de catálogo	Profundidade	Quantidade por embalagem	Acabamento
20835-899	2.5mm	10	Anodized
20835-896		10	
20835-929		10	
20835-931		10	

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

