

Quick Strut Nut



CARACTERISTICI

Provides fast universal attachment of threaded rod and hardware to standard strut profiles

Pre-assembled slide nut ready to use out of the box

Spring retains assembly in place until hardware is tightened

Material: Oțel
Finish: Electrogalvanized

SPECIFICAȚII

Table 1/2

Număr de catalog	Article Number	Rod Size (RS)	A	B	C	Torque (TQ)
QSNM10EG	592920	10	8 mm	4 mm	41 mm	55 N·m
QSNM12EG	592930	12	8 mm	4 mm	41 mm	
QSNM6EG	592900	6	6 mm	4 mm	41 mm	
QSNM8EG	592910	8	6 mm	4 mm	41 mm	28 N·m




Table 2/2

Număr de catalog	Article Number	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
QSNM10EG	592920	4400N	4400N	4900N
QSNM12EG	592930	4400N	4700N	4900N
QSNM6EG	592900	2000N	2000N	2000N
QSNM8EG	592910	3300N	3300N	3300N

DETALII SUPLIMENTARE DESPRE PRODUS

Static Load 1 represents 1.5 mm strut channel thickness. Static Load 2 represents 2.0 mm strut channel thickness. Static Load 3 represents 2.5 mm strut channel thickness.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/CADDY

