

Accesorii de conectare pentru lămpi cu LED, ELC

Cabluri gata de utilizare pentru energia de alimentare, cabluri de intrare și comutatoare de ușă. Cablurile sunt disponibile în culori diferite.

CARACTERISTICI

Descriere: Cabluri prefabricate pentru lămpi cu LED. Utilizarea acestor cabluri va economisi timp și va facilita montarea lămpilor.

Conexiune: Alimentare, cu cabluri cu 3 poli și cablare în serie (alimentarea de 24 V este destinată cablului de 24 V).

Dimensiuni: Lungimi diferite: Consultați lista de articole pentru mai multe informații.



Material: Copper
Finish: Smooth

SPECIFICAȚII

Număr de catalog	Product Family	Color	Length	Cable Type	Connection Type	Package Quantity
ELC3001DU	IEC General Accessories	Black	3000m m	Cable for Door Switch	TPS-Cable for Doorswitch, UL Version	1
ELC1005PB	IEC General Accessories	Black	1000m m	Connection Cable	Infeed, 3 Pole, 100-240 V AC	5
ELC1005PO	IEC General Accessories	Orange	1000m m	Connection Cable	Infeed, 3 Pole, 100-240 V AC	5
ELC1005TB	IEC General Accessories	Black	1000m m	Through Wiring	Trough-Wiring, 3 Pole, 100-240 V AC	5
ELC1005TG24V	IEC General Accessories	Gray	1000m m	Through Wiring	Trough-Wiring, 2-Pole, 24 V (DC)	5
ELC1005TO	IEC General Accessories	Orange	1000m m	Through Wiring	Trough-Wiring, 3 Pole, 100-240 V AC	5
ELC3001DE	IEC General Accessories	Black	3000m m	Cable for Door Switch	TPS-Cable for Doorswitch, ENEC Version	1

Număr de catalog	Product Family	Color	Length	Cable Type	Connection Type	Package Quantity
ELC3005PB	IEC General Accessories	Black	3000m m	Connection Cable	Infeed, 3 Pole, 100-240 V AC	5
ELC3005PG24V	IEC General Accessories	Gray	3000m m	Connection Cable	Infeed, 2-Pole, 24 V (DC)	5
ELC3005PO	IEC General Accessories	Orange	3000m m	Connection Cable	Infeed, 3 Pole, 100-240 V AC	5

DETALII SUPLIMENTARE DESPRE PRODUS

Versiune UL – cablu TPS gata de utilizare pentru întrerupătorul ușii (certificat UL).

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

