

Plinte laterale, PSS



Aceste panouri laterale pentru plintă acoperă spațiul de sub dulap, dacă se impune.

CARACTERISTICI

Descriere: Panouri laterale pentru acoperirea deschiderilor de pe lateralul plintei PFS. Panouri dublu pliate pentru rezistență maximă. Compatibile cu gamele de dulapuri industriale combinabile și compacte din oțel inoxidabil.

Material: Oțel inoxidabil AISI 304 / AISI 316L cu granulație.
Panouri: 1.5 mm.

Finisaj: Oțel inoxidabil pregranulat, 400.

Cantitate pachet: 2 panouri. Accesoriile de montaj sunt incluse în PFS.

SPECIFICAȚII

Număr de catalog	Height	Width	Depth	Product Family	Material	Enclosure Material
PSS1040-316	100mm	400mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS1050	100mm	500mm	27mm	Free-Standing	Stainless Steel 304	Oțel Zincat, Stainless Steel
PSS1080-316	100mm	800mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS1100-316	100mm	999mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS2050	200mm	500mm	27mm	Free-Standing	Stainless Steel 304	Oțel Zincat, Stainless Steel
PSS2060-316	200mm	600mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS2040	200mm	400mm	27mm	Free-Standing	Stainless Steel 304	Oțel Zincat, Stainless Steel
PSS2050-316	200mm	500mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS2080-316	200mm	800mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS1060	100mm	600mm	27mm	Free-Standing	Stainless Steel 304	Oțel Zincat, Stainless Steel
PSS2040-316	200mm	400mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS2060	200mm	600mm	27mm	Free-Standing	Stainless Steel 304	Oțel Zincat, Stainless Steel
PSS1060-316	100mm	600mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS2100-316	200mm	999mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel
PSS1040	100mm	400mm	27mm	Free-Standing	Stainless Steel 304	Oțel Zincat, Stainless Steel
PSS1050-316	100mm	500mm	27mm	Free-Standing	Stainless Steel 316	Oțel Zincat, Stainless Steel

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE