

Ușă plină, DNSS



Această ușă înlocuiește panoul spate al unui dulap industrial, pentru a permite accesul dinspre spate la echipamentele montate în partea din față sau pentru a monta plăcile prin spatele dulapului, cu scopul de a crește spațiul disponibil pentru montaj.

CARACTERISTICI

Descriere: Ușă standard prevăzută cu sistem de încuiere dublu-bit de 3 mm și cadru de ușă. Kit de accesorii pentru ușă DNMM (balamale, tije de prindere) trebuie comandată separat. Permite toate opțiunile aferente programului de încuiere și balamalele cu deschidere la 180°.

Material: Oțel inoxidabil 2 mm AISI 304, AISI 316L (la cerere).

Încărcare max.: 800 N.

Finisaj: Oțel inoxidabil pregranulat, 400.

Cantitate pachet: 1 bucată.

Cerințe montaj: Dacă anterior nu a fost montată o ușă este necesar să folosiți kit-ul DNMMKS.

Material: Stainless Steel 304
Finish: Lustruit
Thickness: 2mm

SPECIFICAȚII

Table 1/2

Număr de catalog	Height	Width	Depth	Door Type	Product Family	Enclosure Material
DNSS1212L	1200mm	600mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS1212R	1200mm	600mm	17mm	Right Door	Free-Standing	Oțel Zincat

Număr de catalog	Height	Width	Depth	Door Type	Product Family	Enclosure Material
DNSS1408	1400mm	800mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1606	1600mm	600mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1608	1600mm	800mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1610	1600mm	1000mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1612L	1600mm	600mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS1612R	1600mm	600mm	17mm	Right Door	Free-Standing	Oțel Zincat
DNSS1806	1800mm	600mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1808	1800mm	800mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1810	1800mm	1000mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS1810L	1800mm	500mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS1810R	1800mm	500mm	17mm	Right Door	Free-Standing	Oțel Zincat
DNSS1812L	1800mm	600mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS1812R	1800mm	600mm	17mm	Right Door	Free-Standing	Oțel Zincat
DNSS1816L	1800mm	800mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS1816R	1800mm	800mm	17mm	Right Door	Free-Standing	Oțel Zincat
DNSS2006	2000mm	600mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS2008	2000mm	800mm	17mm	Single Door	Free-Standing	Oțel Zincat
DNSS2010	2000mm	1000mm	17mm	Single Door	Free-Standing	Oțel Zincat

Table 2/2

Număr de catalog	Height	Width	Depth	Door Type	Product Family	Enclosure Material
DNSS2012L	2000mm	600mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS2012R	2000mm	600mm	17mm	Right Door	Free-Standing	Oțel Zincat
DNSS2016L	2000mm	800mm	17mm	Left Door	Free-Standing	Oțel Zincat
DNSS2016R	2000mm	800mm	17mm	Right Door	Free-Standing	Oțel Zincat

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

