

Ladder Tray Clip for Strut, Hot Dip Galvanized Steel

NÚMERO DE CATÁLOGO

LTC

The nVent CADDY Ladder Tray Clip makes attaching ladder trays to strut profiles quick and easy—featuring a single-piece design, ready for use out-of-the box with no loose hardware.

Offering two simple installation methods, the Ladder Tray Clip can be either installed on top of the strut or slid in from either end of the channel, increasing flexibility and giving contractors more options on the job. Designed for both indoor and outdoor installations, the hot-dip galvanized finish and hardware ensure longevity on rooftop, solar and trapeze projects.

CARACTERÍSTICAS


Single-piece design with hardware pre-installed to reduce components

Simple and time-saving; just drop and twist the Ladder Tray Clip directly into the strut profile

Works on ladder tray with up to ½ in flange thickness

Hot-dip galvanized clamp and hardware for demanding environments

Integrated clamping teeth for superior holding strength and load ratings



CARATERÍSTICAS DO PRODUTO

Número do artigo: 387715

Material: Aço

Acabamento: Hot-Dip Galvanized

Espessura do flange (FT): 13 mm Max

A: 49 mm

B: 38.1 mm

Diâmetro do Parafuso (Sc): 3/8"



Torque (TQ): 41 N·m

Ultimate Static Load 1 (F1): 2225N

Ultimate Static Load 2 (F2): 3100N

Ultimate Static Load 3 (F3): 10675N

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com

