


LHX+ Air/Liquid Heat Exchanger



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. RackChiller IRC is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure.

CARACTERISTICI

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

Depth: 500mm
Product Type: Air/Liquid Heat Exchanger
Airflow Direction: Front to Top

SPECIFICAȚII

Table 1/2

Număr de catalog	Fan Quantity	Input Voltage AC	Package Quantity	Supply Voltage	Redundant Power Supply	Coolant Feed
29714-017	1	100 – 240V	1	230V min	No	Bottom
29714-016	2	100 – 240V	1	230V min	No	Bottom

Table 2/2

Număr de catalog	Height	Material	Product Family	Width	Works With
29714-017	266mm	Aluminiu	Cooling	426mm	Varistar, Varistar CP
29714-016	266mm	Aluminiu	Cooling	426mm	Varistar, Varistar CP

DETALII SUPLIMENTARE DESPRE PRODUS

Please order separately: Monitoring via Control unit, water control package, display and door contact switch.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE