


Uniklip Variable Riser



CARACTERÍSTICAS

Creates a quick and easy vertical pathway transition

Provides optimal support for high-performance low voltage and data cables

Innovative UNIKLIP installation system that installs up to three times faster

IEC 61537 load rating and earthing compliant

No field cutting or modifications required; just drop it in and keep installing the cable tray

Eliminates safety related concerns around field cutting



Tool-free, integrated couplers with Uniklip

Material: Aço
Acabamento: Pregalvanized



ESPECIFICAÇÕES

Número de catálogo	Número do artigo	Largura (W)	Altura (H)	Ângulo (a)	A	B	C
PCT50X050VR90	850200	50 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X075VR90	850210	75 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X100VR90	850220	100 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X150VR90	850230	150 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X225VR90	850240	225 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X300VR90	850250	300 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X450VR90	850260	450 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X500VR90	850270	500 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X600VR90	850280	600 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

