

Wire Basket Tray Drop Out



The nVent CADDY Wire Basket Tray Drop Out is a versatile solution for creating cable management exits in cable tray. By acting as a wire funnel, the Drop Out enables cables to easily drop vertically from the tray while ensuring proper support and protecting the bend radius at the exit point. The tool-free design allows installers to drop the component into place on the wire basket tray while the side prongs hold it firmly in place. Whether contractors are working with multi-tier assemblies or side-by-side configurations, the Drop Out offers an aesthetic and efficient way to manage cable transitions, without compromising on performance or accessibility.

CARACTERÍSTICAS

Designed for center cable tray dropouts

Conducive to creating both multi-tier tray and side-by-side assemblies

Easily cut to fit around the wire basket tray for retrograde cable installations

Ensures the natural bend radius of the cable is protected

Stackable for multiple adjoining dropouts

Reusable and tool-free—easy-to-install, easy-to-remove


Material: ABS, UL-VO rated

Acabamento: Pregalvanized

ESPECIFICAÇÕES

Número de catálogo	Altura (H)	Largura (W)	Length (L)	Peso unitário
WBTCBLDO	28.6 mm	58.74 mm	90.5mm	0.05 kg
WBTCBLDO4	28.6 mm	109.3 mm	92.08mm	0.01 kg
WBTCBLDO6	29.4 mm	158 mm	210.85mm	0.02 kg

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

