

Fönstersatser för farliga platser



Hazardous Location Window Kits are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. These window kits ensure a dust-, oil-, and water-tight seal. Designed for use as viewing windows, these window kits are ideal for visibility of internal enclosure components. The windows are easily installed by making a cutout in the enclosure and attaching the window and frame with included mounting hardware.

BRANSCHSTANDARDER

UL 508A Component Recognized; Type 4, 4X, 12, 3R; File No. E61997

IECEx and ATEX Approvals

Suitable for use on increased safety enclosures for ZONE 1 or ZONE 2 assemblies

ATEX Directive 94/9/EC

ATEX

Sira 13ATEX3315U

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEx

IECEx SIR 13.0123U

Ex e IIC Gb

Ex tb IIIC Db IP 66

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12,

3R; File No. E61997

NEMA/EEMAC 4, 4X, 12, 13

IEC 60529, IP66

DESIGN

Secure sealing with silicon gasket to protect against water and dust ingress in high-temperature applications

Maintain visual on components through .25-in. (6-mm) tempered safety glass

Easy installation in enclosure cutouts with window frame hardware

Material: Rostfritt stål 316L

SPECIFIKATIONER

Katalognummer	Tjocklek	Utskärningsstorlek
EXWK53SS6	1.98mm	170 x 119mm
EXWK138SS6	1.98mm	373 x 246mm
EXWK1711SS6	1.98mm	475 x 322mm
EXWK2315SS6	1.98mm	627 x 424mm
EXWK2919SS6	1.98mm	780 x 526mm
EXWK711SS6	1.98mm	221 x 322mm
EXWK715SS6	1.98mm	424 x 221mm
EXWK720SS6	1.98mm	221 x 551mm
EXWK724SS6	1.98mm	221 x 653mm
EXWK729SS6	1.98mm	221 x 780mm
EXWK95SS6	1.98mm	272 x 183mm

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

