


# 加固型组件的装配零件



带放松脱螺纹油的装配零件，适用于加固型侧面板、水平横梁、盖板、后角。

### 功能

用于下列固定件的螺钉：加固型侧板 - 水平横梁, 加固型侧板 - 盖板, 加固型侧板 - 后角轨

产品系列: EuropacPRO  
产品类型: 装配组件



### 技术参数

| 物料号       | 类型   | 长度   | 包装数量 | 螺纹尺寸 | 完成 | 材料  | 搭配 |
|-----------|------|------|------|------|----|-----|----|
| 24566-100 | 沉头螺钉 | 18mm | 100  | M4   |    | 不锈钢 | 插箱 |
| 24566-101 | 沉头螺钉 | 14mm | 100  | M4   |    | 不锈钢 | 插箱 |
| 24560-140 | 方螺母  |      | 100  |      | 镀锌 | 钢   | 插箱 |
| 24566-102 | 盘头螺钉 | 14mm | 100  | M4   |    | 不锈钢 | 插箱 |
| 24566-103 | 盘头螺钉 | 10mm | 100  | M4   |    | 不锈钢 | 插箱 |
| 24566-104 | 盘头螺钉 | 8mm  | 100  | M4   |    | 不锈钢 | 插箱 |
| 24566-105 | 沉头螺钉 | 7mm  | 100  | M4   |    | 不锈钢 | 插箱 |
| 24566-106 | 沉头螺钉 | 10mm | 100  | M4   |    | 不锈钢 | 插箱 |

### 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

## North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

