

MTCA.4 填充模块，带空气挡板，全尺寸，双

物料号

21850-107

通过锁固部件盖住 MTCA.1 和 MTCA.4 系统中未使用的 AdvancedMC、MCH 或 PM 电源 插槽，或 MTCA.0 系统中未使用的插槽。模块由带门锁和紧固螺丝的前面板、EMC 垫片和侧面板组成。模块可以通过外加螺钉固定至卡笼。

功能

符合 MicroTCA.1 和 MicroTCA.4 规范

用于遮盖 MicroTCA.1 或 MicroTCA.4 系统内的空插槽

带法兰和 M3 固定螺丝，用以将模块固定到机箱卡笼

EMC 屏蔽



产品属性

设计特征: 全尺寸

包装数量: 1

材料: 不锈钢

产品系列: MicroTCA

产品类型: 系统模块

类型: 填充模块

净重: 0.38kg

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF

工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE