

底座前后盖板，PF

The front and rear plinth allows for cabling without any restrictions in accordance with the VDE 0113 standard. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

功能

Description: Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each side for added strength.

Material: Corner pieces in 2 mm and panels in 1.5 mm mild steel.

Finish: RAL 7022 structured powder coating.

Pack quantity: 1 set of 4 corner pieces including covers. Front and rear panel (2 rear panels for 200 mm high plinths) with mounting accessories. Mounting accessories for side panels PS or transversal profiles PCP.

Mounting requirements: Add the side panels PS for a complete plinth. When combining enclosures it is recommended to add transversal panels PCP for cable duct support and extra rigidity.



厚度:	1.5mm
材料:	低碳钢
完成:	粉末涂层
颜色代码:	RAL 7022
颜色:	本影灰

技术参数

物料号	订货号	高度	宽度	深度	产品系列	外壳材料
PF1120	PF1120	100mm	1200mm	63mm	独立	低碳钢
PF1100	PF1100	100mm	1000mm	63mm	独立	低碳钢
PF2120	PF2120	200mm	1200mm	63mm	独立	低碳钢
PF1060	PF1060	100mm	600mm	63mm	独立	低碳钢
PF1080	PF1080	100mm	800mm	63mm	独立	低碳钢
PF2040	PF2040	200mm	400mm	63mm	独立	低碳钢
PF1050	PF1050	100mm	500mm	63mm	独立	低碳钢
PF2100	PF2100	200mm	1000mm	63mm	独立	低碳钢
PF2050	PF2050	200mm	500mm	63mm	独立	低碳钢
PF2060	PF2060	200mm	600mm	63mm	独立	低碳钢
PF1040	PF1040	100mm	400mm	63mm	独立	低碳钢
PF2080	PF2080	200mm	800mm	63mm	独立	低碳钢

其他产品详情

For enclosures 1600 mm wide use 2 x 800 mm wide plinth.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE