

提拉锁锁芯系统，LHC



The locking inserts and cylinders can be mounted independently in the lift handle, which means many combinations can be created. This reduces the number of handles to be stocked.

功能

Description: Profile half cylinder locks. To be used in the lift handles LHC.

Pack quantity: 1 piece.

完成: 平滑哑光

颜色: 黑灰色

技术参数

物料号	订货号	高度	宽度	深度	密钥类型	密钥代码
LHC521	LHC521	37mm	23mm	41mm	Ronis	C21323
LHC5212132E	LHC5212132E	37mm	23mm	41mm	Ronis	2132E
LHC5213121E	LHC5213121E	37mm	23mm	41mm	Ronis	3121E
LHC522	LHC522	37mm	23mm	41mm	Ronis	C21323
LHC523	LHC523	37mm	23mm	41mm	方形 7 毫米	
LHC524	LHC524	37mm	23mm	41mm	方形 8 毫米	
LHC526	LHC526	37mm	23mm	41mm	三角形 7 毫米	
LHC527	LHC527	37mm	23mm	41mm	三角形 8 毫米	
LHC528	LHC528	37mm	23mm	41mm	双刀头 3 毫米	
LHC529	LHC529	37mm	23mm	41mm	双刀头 5 毫米	
LHC530	LHC530	37mm	23mm	41mm	戴姆勒·奔驰	
LHC531	LHC531	37mm	23mm	41mm	带槽锁芯插件 2x4 毫米	
LHC533	LHC533	37mm	23mm	41mm	锁芯 N°E1 (大众)，不含钥匙	
LHC534	LHC534	37mm	23mm	41mm	适用于其它半圆柱形锁芯的适配器 (DIN18252)	

物料号	订货号	高度	宽度	深度	密钥类型	密钥代码
LHC535	LHC535	37mm	23mm	41mm	适用于 ASSA ABLOY 和 Trioving 锁芯的适配器	
LHC536	LHC536	37mm	23mm	41mm	Push button only	

其他产品详情

* Other key numbers available on request. ** Key numbers 333, 1333, EK333 and GX130 are equal. *** Order separate key LSMK for Square 8 mm and Triangle 8 mm.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

