

# Partial Doors For Floor Standing Enclosures, DP

Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.



## 功能

**Description:** To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

**Material:** 1.75 mm steel plate.

**Finish:** RAL 7035 structured powder coating.

**Protection:** Complies with IP 44.

**Pack quantity:** 1 door with hinges, locks and mounting accessories.

**Mounting requirements:** Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

颜色: 浅灰色  
材料: 低碳钢  
完成: 粉末涂层  
颜色代码: RAL 7035

技术参数

| Table 1/2 |        |       |      |      |      |
|-----------|--------|-------|------|------|------|
| 物料号       | 高度     | 宽度    | 深度   | 产品系列 | 外壳材料 |
| DP01506R5 | 150mm  | 600mm | 17mm | 独立   | 低碳钢  |
| DP10008R5 | 1000mm | 800mm | 17mm | 独立   | 低碳钢  |
| DP03006R5 | 300mm  | 600mm | 17mm | 独立   | 低碳钢  |
| DP02506R5 | 250mm  | 600mm | 17mm | 独立   | 低碳钢  |
| DP01508R5 | 150mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP04006R5 | 400mm  | 600mm | 17mm | 独立   | 低碳钢  |
| DP05006R5 | 500mm  | 600mm | 17mm | 独立   | 低碳钢  |
| DP02004R5 | 200mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP06008R5 | 600mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP12006R5 | 1200mm | 600mm | 17mm | 独立   | 低碳钢  |
| DP06004R5 | 600mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP08006R5 | 800mm  | 600mm | 17mm | 独立   | 低碳钢  |
| DP02504R5 | 250mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP04004R5 | 400mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP05004R5 | 500mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP03008R5 | 300mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP10006R5 | 1000mm | 600mm | 17mm | 独立   | 低碳钢  |
| DP02008R5 | 200mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP08008R5 | 800mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP02006R5 | 200mm  | 600mm | 17mm | 独立   | 低碳钢  |

| Table 2/2 |        |       |      |      |      |
|-----------|--------|-------|------|------|------|
| 物料号       | 高度     | 宽度    | 深度   | 产品系列 | 外壳材料 |
| DP03004R5 | 300mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP01504R5 | 150mm  | 400mm | 17mm | 独立   | 低碳钢  |
| DP12008R5 | 1200mm | 800mm | 17mm | 独立   | 低碳钢  |
| DP02508R5 | 250mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP05008R5 | 500mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP04008R5 | 400mm  | 800mm | 17mm | 独立   | 低碳钢  |
| DP06006R5 | 600mm  | 600mm | 17mm | 独立   | 低碳钢  |

## 警告

---

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE