

Partial Panels For Floor Standing Enclosures, DPP



Partial panels allow for many different, easily accessible, configurations of separate compartments within the enclosure. The panels are secured with screws, which ensures that it can only be removed by service personnel, to improve the operators safety.

功能

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CDHK when no door is required.

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 54.

Pack quantity: 1 panel with mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

材料:	低碳钢
完成:	粉末涂层
颜色:	浅灰色
颜色代码:	RAL 7035
厚度:	1.75mm

技术参数

物料号	高度	宽度	深度	产品系列	外壳材料
DPP01004R5	100mm	400mm	17mm	独立	低碳钢
DPP01006R5	100mm	600mm	17mm	独立	低碳钢
DPP01008R5	100mm	800mm	17mm	独立	低碳钢
DPP01504R5	150mm	400mm	17mm	独立	低碳钢
DPP01506R5	150mm	600mm	17mm	独立	低碳钢
DPP01508R5	150mm	800mm	17mm	独立	低碳钢
DPP02004R5	200mm	400mm	17mm	独立	低碳钢
DPP02006R5	200mm	600mm	17mm	独立	低碳钢
DPP02008R5	200mm	800mm	17mm	独立	低碳钢
DPP02504R5	250mm	400mm	17mm	独立	低碳钢
DPP02506R5	250mm	600mm	17mm	独立	低碳钢
DPP02508R5	250mm	800mm	17mm	独立	低碳钢
DPP03004R5	300mm	400mm	17mm	独立	低碳钢
DPP03006R5	300mm	600mm	17mm	独立	低碳钢
DPP03008R5	300mm	800mm	17mm	独立	低碳钢
DPP04004R5	400mm	400mm	17mm	独立	低碳钢
DPP04006R5	400mm	600mm	17mm	独立	低碳钢
DPP04008R5	400mm	800mm	17mm	独立	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

