

Ușă vitrată, ADCS



Componentele electrice sunt vizibile cu ușa închisă, ceea ce permite menținerea protecției împotriva factorilor externi și împiedică accesul personalului neautorizat.

CARACTERISTICI

Descriere: Montată pentru a înlocui ușa standard, asigură o imagine clară asupra componentelor instalate în cofret. Permite toate opțiunile aferente programului de închidere.

Material: Oțel inoxidabil 1.5 mm, AISI 304, 2 mm pentru și cofrete cu o înălțime sau lățime de 600 mm sau mai mare, 4 mm sticlă securizată transparentă.

Finisaj: Oțel inoxidabil pregranulat, 400.

Protecție: Conformă cu IP 55 | TYPE 12, 13, IK 07.

Cantitate pachet: 1 buc.

The glazed door allows the electrical components to be seen while the enclosure's door is closed

The user can monitor the status of the components without the need for opening the enclosure's door maintaining the ingress protection

Material: Stainless Steel 304

Finish: Lustruit

Thickness: 1.5mm

SPECIFICAȚII

Număr de catalog	Height	Width	Latch Quantity	Window Size	Product Family	Enclosure Material
ADCS03624	360mm	240mm	1	219 x 83mm	Wall Mounted	Oțel Zincat
ADCS04030	400mm	300mm	1	259 x 143mm	Wall Mounted	Oțel Zincat

Număr de catalog	Height	Width	Latch Quantity	Window Size	Product Family	Enclosure Material
ADCS04040	400mm	400mm	1	259 x 243mm	Wall Mounted	Oțel Zincat
ADCS04060	400mm	600mm	1	259 x 443mm	Wall Mounted	Oțel Zincat
ADCS05040	500mm	400mm	1	359 x 243mm	Wall Mounted	Oțel Zincat
ADCS05050	500mm	500mm	1	359 x 343mm	Wall Mounted	Oțel Zincat
ADCS06040	600mm	400mm	2	459 x 243mm	Wall Mounted	Oțel Zincat
ADCS06060	600mm	600mm	2	459 x 443mm	Wall Mounted	Oțel Zincat
ADCS06080	600mm	800mm	2	459 x 643mm	Wall Mounted	Oțel Zincat
ADCS08060	800mm	600mm	2	659 x 443mm	Wall Mounted	Oțel Zincat
ADCS08080	800mm	800mm	2	659 x 643mm	Wall Mounted	Oțel Zincat
ADCS10080	1000mm	800mm	1	859 x 643mm	Wall Mounted	Oțel Zincat
ADCS12080	1200mm	800mm	1	1059 x 643mm	Wall Mounted	Oțel Zincat
ADCS14080	1400mm	800mm	1	1259 x 643mm	Wall Mounted	Oțel Zincat

DETALII SUPLIMENTARE DESPRE PRODUS

* Încuietoare tip espagnolette în 3 puncte. Nepotrivit pentru AFS.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

