


Cooling Circuitry STD 3U 76TE mont. W/ QD

New

物料号

20740-050

The Easy Swap LFT Cooling Circuit is a "back-pack" cooling Unit for a 3U subrack rear area. With its width of 76 HP it allows an additional 8 HP front panel to be mounted aside for the mains power inlet to the subrack. Up to 3 Easy Swap Cold plates can be attached to the unit either by the Easy Swap LFT Direct Connection Set or the Quick Disconnect Set. It dissipates the heat of the Cold Plates with a heat exchanger and 2 low noise fans to the back.

功能

Cooling Circuitry for up to 3 Easy Swap LFT Cold Plates

3 U height, 76 HP width. Can be mounted at the backside of a 3U subrack

Up to 600 W of cooling capacity at 50°C environmental temperature

Accepts demineralized water or Water Glycol mix (25% Glycol recommended)

Low noise fans and pump

Easy Swap LFT Cold Plates can be connected to Cooling Circuitry either with Direct Connection Set or Quick Disconnect Set



产品属性

包装数量: 1

产品系列: 板卡级液冷

产品类型: 导体块

类型: Liquid Cooling Circuitry

宽度: 383.8mm

搭配: 插箱

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

Please order the Cold Plates and Connection sets separately

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	

